Cable and wiremarking

Wicon wrap-around system









Wicon* wrap-around applicator system

The Wicon system will automate your wire and cable identification process and can increase the production output significantly.

Cylindric items of diameters 2 mm to 16 mm, such as single wires, strands, cables, hoses, tubes or round rods, can be labeled with the wrap-around applicator.

Transparent laminate protects data blocks persistently from environmental impacts.

Items are inserted in horizontal orientation and centered by panels. They can be aligned 25 mm to 100 mm (1" to 4") distant to the margin of a label using a stop.

Printing a label and wrapping it around an item takes 1.8 to 6 seconds, depending on the number of wrap-arounds.

Operation starts as soon as an item has been inserted. It may be triggered also by a foot switch, a data interface or an I/O interface. A label is printed and then picked up by the applicator. The diameter of an item is identified on the wrapper head. The size of a label determines how many times it will be wrapped around the item.

A finger guard covering the feed opening prevents items from being inserted or removed during wrapping around.

Only wrap-around labels provided by the manufacturer guarantee reliable applications. Make sure item surfaces are clean and free of lubricants.

Pivoting the applicator allows label rollsor ribbons been replaced easily.

A service door enables access to the wrapper head in cases of errors, such as label jams.



*Trade product, no LAPP product.

Wrap-around applicator _____

Technical	data			WICON		
Item	Diameter		ım	2.0-16.0		
	Length n	nm at lea	st	132		
	Centering panel distant to left and right	m	ım	124		
	Label margin distant to centering panel	•				
	Label margin distant to edge of item by stop	m	25-100			
	Deflection related to a length of 124 mm	m	ım	max. 1		
Label	Width	m	m	12.7-50.8		
	Height	m	m	19.1–70.0		
Applicator	Cycle time printing and applying			1.8-6		
	or applying and printing					
	Number of wrap-arounds			2-10		
Start	As soon as an item has been inserted by hand					
	or via data interface					
	or via I/0 interface					



Label printer _____

Technical	data	SQUIX 4/MP		
Materials	guided on the pr	centered		
Print meth	nod	Thermal transfer		
Print reso	lution	dpi	300	
Print speed		mm/s max.	200	
Print widt	h	mm max.	105.7	
Finishing	Roll diameter	mm max.	205	
	Core diameter	mm	76	

Label margins are at least 12.7 mm distant to the outside of the centering panel. Moving the applicator aligns the outside of a liner material to the marking.

Label margins can be set 25 mm to 100 mm distant to the edge of an item using the stop.

- \bullet The stop can be rotated by 180°
- Narrow side with small item diameters
- Wider side with item diameters 5 mm or more.

Article list _

Article no. Label printer
83259579 SQUIX 4/300MP label printer



Article no. Applicator

83259569 WICON wrap-around applicator Included in the accessory pack are:

• DR4-M60 print roller



DR4-M60 print rollerWICON peel-off plate

Optional accesories are available. Please ask for furher information.



Wrap-around labels

Transparent laminate covers data blocks and protects them persistently from environmental impacts.


Labels can be removed from the peel-off plate of a printer by hand or transfered by the wrap-around applicator directly to items.

The labels are wound in single lanes.

With labels 19.1 mm to 63.5 mm high (H), items diameters 2 mm to 16 mm can be labeled. If using labels 70 mm high, the item diameter must be 6 mm or more.


All-around labeling

Up to the D1 diameter value, a data block captures the circumference of an item.



Partial labeling

Up to the D2 diameter value, protective laminate captures a data block.



В –

Article list

rticie iist _								
Article no.	Data block color	Product D1 mm	Ø D2 mm	Label width B mm	Label height H mm	Data block height P mm	No. of labels per roll	VPE 1 Single roll
83259970	white	2.0	4.0	12.7	19.1	6.4	7,450	1
83259971	white	2.0	4.0	25.4	19.1	6.4	7,450	1
83259972	white	3.0	5.0	25.4	25.4	9.5	5,800	1
83259973	white	4.0	8.0	12.7	38.1	12.7	4,000	1
83259974	white	4.0	8.0	19.1	38.1	12.7	4,000	1
83259975	white	4.0	8.0	25.4	38.1	12.7	4,000	1
83259976	white	4.0	8.0	50.8	38.1	12.7	4,000	1
83259977	white	6.0	14.0	25.4	63.5	19.1	2,450	1
83259978	white	6.0	14.0	38.1	63.5	19.1	2,450	1
83259979	white	6.0	16.0	25.4	70.0	19.1	2,250	1
83259980	white	6.0	16.0	50.8	70.0	19.1	2,250	1

Further sizes, colors and materials can be provided upon request.

Material: Vinyl (PVC) Thickness: 80 µm Adhesive: Permanent Temperature: -40 to 80 °C Operation: Indoor, outdoor

Resistances: Water, dirt, petrol, oils, alcohol,

detergents, UV light

Roll finishing: Outside diameter max. 205 mm

core diameter 76 mm

Ribbons

One ribbon roll serves for printing two rolls of wrap-around labels.



Article list _

Article no.	Width mm	Length mm
83259604	55	360

Material: R71 resin, black, inside color layer

Scopes of delivery, designs and technical data correspond to the date of this publication. They are subject to change.



P O Box 1022, SE-611 29 Nyköping · Visit: Kungshagsvägen 9 Phone: +46 (0)155 777 90 · info.se.fln@lapp.com · www.fleximark.com









