


	DATA SHEET	
Valid from: 2016-05-02	FLEXIMARK® Cable tie collars	

FLEXIMARK® Cable tie collars for LMB and TMB labels.
Mounted with FLEXIMARK® Cable ties.



Technical data

Material:	PUR halogen-free (HF) PVC
Operating temperature:	PUR -60°C to +80°C PVC -15°C to +70°C
Colour:	Transparent

Mounting:

Use FLEXIMARK® Cable ties.


Other product data:

ETIM Classification:	EC001288
----------------------	----------

Advantages:

- Easy, durable collar for markings.
- Scratch resistant.
- Different sizes.
- PVC material have UL94 V0.

Creator: Fleximark/LR	Document: DB83252676EN Cable tie collars Version: 00	Page 1 of 2
-----------------------	---	-------------

	DATA SHEET	
Valid from: 2016-05-02	FLEXIMARK® Cable tie collars	

Product data:

E-number	Lapp article no.	Article designation	Length mm	Colour	Halogen-free	Pieces/PU
2972279	83252676	Cable tie collar transp. HF 30 mm	30	Transparent	Yes	200
2972280	83252640	Cable tie collar transp. 30 mm	30	Transparent	No	200
2941158	83290190	Cable tie collar transp. 23	23	Transparent	No	200
1516665	83252639	Cable tie collar 20x9.3 mm	20	Transparent	No	240

Related products

FLEXIMARK® Cable tie collars are suitable for FLEXIMARK® LMB and FLEXIMARK® TMB labels as well as 3M™ Trasp™ characters. Easily mounted with FLEXIMARK® Plastic cable ties.



Note:

Pictures are not to scale and do not represent detailed images of each product.

Creator: Fleximark/LR	Document: DB83252676EN Cable tie collars Version: 00	Page 2 of 2
-----------------------	---	-------------