

	DATA SHEET	
Valid from: 18-01-2019	FLEXIMARK® Marking kit DYMO Rhino 4200	

Portable marking kit with accessories for cable and component marking.
Includes DYMO Rhino Marking tape, Label printer Rhino 4200 and FLEXIMARK® Character holders.
Delivered in a solid and robust case.
Available as two different kit with tapes and holders in two sizes 9 mm and 12 mm.
Label printer DYMO Rhino 4200 with (QWERTY) keyboard layout and many more features.



Product data:

Included in the FLEXIMARK® Marking kit DYMO Rhino 4200 (9 mm):

Label printer DYMO Rhino 4200	1pcs
DYMO Rhino Marking tape Vinyl black, 9 mm	1pcs
DYMO Rhino Marking tape Vinyl white, 9 mm	1pcs
FLEXIMARK® Character holders PTE, 9,5 mm x 10 m	1pcs
FLEXIMARK® Plier FL52ERA for character holders, 6-12 mm	1pcs
FLEXIMARK® Plastic cable ties black, 135x2.6 mm	100pcs

Included in the FLEXIMARK® Marking kit DYMO Rhino 4200 (12 mm):

Label printer DYMO Rhino 4200	1pcs
DYMO Rhino Marking tape yellow, 12 mm	1pcs
DYMO Rhino Marking tape white, 12 mm	1pcs
FLEXIMARK® Character holders PTE, 12 mm x 10 m	1pcs
FLEXIMARK® Plier FL52ERA for character holders, 6-12 mm	1pcs
FLEXIMARK® Plastic cable ties black, 135x2.6 mm	100pcs

Product data:

Part no.	Article designation	Tape width (mm)	Holder width (mm)	Content (unit)	PU
83257103	Marking kit Rhino 9 mm	9	9	1	1
83257104	Marking kit Rhino 12 mm	12	12	1	1

DATA SHEET



Valid from:
18-01-2019

FLEXIMARK® Marking kit DYMO Rhino 4200

Technical data, case:

Size: 38 x 45 x 13,5 cm
Weight: 2,5kg

Technical data, Label printer DYMO Rhino 4200:

Size: 17,8 x 11,7 x 5,7 cm
Weight: 0,91kg
Power: 6 "AA" batteries or lithium ion battery (not included)
Keyboard layout: QWERTY
One-touch formatting keys: Wire and cable wraps
Barcodes
Fixed-length labels
Breaker labels
Shrink tube marking
More features: Favorite keys
Custom keys
Tape: Widths: 6, 9, 12 and 19 mm



Technical data, Vinyl marking tape DYMO Rhino:

Vinyl marking tape: Strong adhesive and high resistance towards chemicals
Colors are adapted to standards: ANSI Z535
ISO3864
ANSI A 13.1
ISO7010
ANSI606-B
Temperature range: -18 up to +90°C



Technical data, FLEXIMARK® Character holders PTE:

Material PTE: Polyethylene, halogen free
Temperature range: -75°C up to +80°C
Resistance: UV-resistant
Approvals: UV-resistance, ageing resistance, resistance towards chemicals
(SP Tested by a third independent expert)



Delivery:

Delivered in a robust case.

Mounting:

All articles needed for mounting cable and component marking are included in the FLEXIMARK® Marking kit. FLEXIMARK® Character holders PTE are produced with FLEXIMARK® Plier FL52ERA for character holder. Cable marking is mounted together with FLEXIMARK® Plastic cable ties and DYMO Rhino Marking tapes.

Other product data:

ETIM Classification: EC001288

Advantages:

Marking for both cables and components
Produce your own marking directly on site
Everything you need for marking in one robust case
Portable label printer DYMO Rhino 4200 with many useful features
Many different DYMO Rhino Marking tapes in assortment

	DATA SHEET	
Valid from: 18-01-2019	FLEXIMARK® Marking kit DYMO Rhino 4200	

Related products:

DYMO Rhino Tape materials available in FLEXIMARK® Marking assortment:

Vinyl
Polyester
Nylon
Shrink tube
Adhesive free
Wraparound vinyl

FLEXIMARK® Character holder PTE sizes in FLEXIMARK® Assortment:

6 mm
9,5 mm
12 mm
15 mm
19 mm

Note:

Pictures are not to scale and do not represent detailed images of each product.

Creator: Fleximark/LR	Document: DB83257 103EN FLEXIMARK Marking kit DYMO Rhino 4200 Version: 02	Page 3 of 3
-----------------------	---	-------------