

	DATA SHEET	
Valid from: 17.10.2022	DYMO XTL™ marking kit & marking tape	

Cable and component marking.
Indoor and outdoor marking.
DYMO® XTL™ marking kit with industrial label maker XTL™ 500.



Delivery:

DYMO® XTL™ marking kit is delivered in a bag with label marker, marking tape, batteries, charger and quick guide.

Other product data:

ETIM Classification: EC001288

Advantages:

- Marking in one bag for both cables and components.
- Can be used both for indoor and outdoor marking.
- Time-saving features to simplify labelling.
- On screen print preview and colour display.
- Built-in label application s make getting started easy.
- Pre-loaded label templates ensure perfect formatting to save time.
- Many different industrial label types available.

Related products:

For the DYMO® XTL™ Marking kit there are many different labels available in the assortment, such as multifunctional vinyl, permanent polyester, shrink tube, laminated cable label and preformatted labels.

Storage:

Cool and dry in original packaging.

	DATA SHEET	
Valid from: 17.10.2022	DYMO XTL™ marking kit & marking tape	

Technical data Marking kit with XTL™ 500:

Printing system XTL 500:	Heat transfer
Maximum label width:	54mm
Label type:	DYMO XTL
Screen size:	109.22 mm colour
Print speed:	28 mm/s
Keyboard:	QWERTY
Resolution:	300 dpi
Printable rows:	24
Barcodes:	Code 128 (Auto), Code 39, code 39 Mod, EAN8, EAN13, UPC-A, Codabar, PDF-417, QR Code
Knife:	Automatic
Memory:	41MB
PC connection:	Yes
Software:	DYMO ID (free of charge, downloadable)
Compability:	Windows 7 and later

Included in package:

- Label printer DYMO XTL 500.
- Charger and USB cable.
- Rechargeable lithium-polymer batteries.
- 1st 54mm x 7m cassette multi-function vinyl, BK/WH.
- 1st 38mm x 39mm laminated cord-/cable marking, black/white, 150 labels.
- Quick guide & Card for software download.



Product data:

Art. no.	Article type	Packaging unit	Unit
83257107	FLEXIMARK DYMO XTL Kit 500 54	1	1
Accessories			
83257221	FLEXIMARK DYMO XTL 500 AC ADAPTER	1	1
83257222	FLEXIMARK DYMO XTL 500 Cutter	1	1
83257223	FLEXIMARK DYMO XTL 500 Li-14.8V Battery	1	1

	DATA SHEET	
Valid from: 17.10.2022	DYMO XTL™ marking kit & marking tape	

Industrial labels for tough environments.
 Many different label types available.
 Suits DYMO® XTL™ 300 Label printer or DYMO® XTL™ 500.



Delivery:

DYMO® XTL™ Marking tapes are delivered separately.

Other product data:

ETIM Classification: EC001288

Advantages:

- Many different industrial label types available
- High resistance towards moisture, UV, chemicals and much more
- Applicable on many different usage areas
- UL969 approval (Standard for Marking and Labelling Systems)

Storage:

Cool and dry in original packaging.

	DATA SHEET	
Valid from: 17.10.2022	DYMO XTL™ marking kit & marking tape	

DYMO XTL™ LAMINATED MARKING TAPE

Advantages Laminated marking tape:

Industrial laminated cable wraps.
Pre-sized with laminated overwrap to protect printing area.
Resistance towards chemicals, oil, moisture, abrasion and fading.
UL recognized as a component to UL968.

Technical data Laminated marking tape:

Material:	Vinyl
Temperature range:	-40°C to +80°C
Mounting surface:	Round surface
Usage:	Indoor
Resistance:	UV, oil, moisture, chemicals
UL Approved:	UL969, RoHS

Product data Laminated marking tape:

Art. no.	Article type	Colour	Size (mm)	Packaging unit	Unit
83257120	FLEXIMARK DYMO XTL Label LAM 21x39WH	White	21x39	150	1
83257123	FLEXIMARK DYMO XTL Label LAM 38x39WH	White	38x39	150	1

DYMO XTL™ FLAT MARKING TAPE

Advantages Flat marking tape:

Industrial label for flat surfaces.
Marking of panels etc.
Transparent blank surface on label for professional appearance.
UL identified as component to UL969.

Technical data Flat marking tape:

Material:	Polyester
Temperature range:	-40°C to +60°C
Mounting:	Flat and structured surfaces
Usage:	Indoor and outdoor
Resistance:	UV, oil, moisture, chemicals
UL Approval:	UL969, RoHS
Colour standard:	OSHA, ANSI, ISO

Product data Flat marking tape:

Art. no.	Article type	Colour	Size (m)	Packaging unit	Unit
83257141	FLEXIMARK DYMO XTL Label Flat 9WH	White	9.1	1	1

	DATA SHEET	
Valid from: 17.10.2022	DYMO XTL™ marking kit & marking tape	

DYMO XTL™ Vinyl MARKING TAPE

Advantages Vinyl marking tape:

Industrial multi-function vinyl label.

Ideal for indoor and outdoor marking.

Resistance towards moisture, chemical and UV.

Wide range of colours to fit with OSHA, ANSI and ISO colour standards and workplace communication and safety.

UL recognised as a component to UL969.

Technical data Vinyl marking tape:

Material:	Vinyl
Temperature range:	-40°C to +60°C
Mounting:	Flat, round and structured surface, flag label
Usage:	Indoor and outdoor
Resistance:	UV, oil, moisture, chemicals
UL Approval:	UL969, RoHS
Colour standard:	OSHA, ANSI, ISO

Product data Vinyl marking tape:

Art. no.	Article type	Colour	Size (m)	Packaging unit	Unit
83257150	FLEXIMARK DYMO XTL Label VIN 54BK/TR	Transparent	7	1	1
83257156	FLEXIMARK DYMO XTL Label VIN 12BK/WH	White	7	1	1
83257157	FLEXIMARK DYMO XTL Label VIN 19BK/WH	White	7	1	1
83257158	FLEXIMARK DYMO XTL Label VIN 24BK/WH	White	7	1	1
83257160	FLEXIMARK DYMO XTL Label VIN 54BK/WH	White	7	1	1
83257178	FLEXIMARK DYMO XTL Label VIN 24BK/YE	Yellow	7	1	1
83257180	FLEXIMARK DYMO XTL Label VIN 54BK/YE	Yellow	7	1	1

Note:

Pictures are not to scale and do not represent detailed images of each product.

Creator: Fleximark/LR	Document: DB83257106EN DYMO XTL Marking kit and tape Version: 03	Page 5 of 5
-----------------------	---	-------------