


	DATA SHEET	
Valid from: 21-01-2019	FLEXIMARK® CHARACTER HOLDERS CAB	

Cable and pipe marking on site.
Indoor and outdoor environment.
Used together with FLEXIMARK® Marking system and 3M™ DYMO™ Industrial marking labels.
Available in different widths and lengths.
Delivered with cable ties.
Premade holes for mounting with plastic cable ties.



Technical data

Material:	Polyethylene, halogen free
Temperature range:	-75°C up to +80°C
Resistance:	UV-resistant
Recommended storage:	Cool and dry in original packaging

Mounting:

FLEXIMARK® Character holders CAB are used for cable marking and mounted with cable ties.

Other product data:

ETIM Classification:	EC001288
----------------------	----------


Advantages:

Produce marking on site when need it.
Easy marking together with 3M™ DYMO™ Industrial marking labels and FLEXIMARK® Marking systems.
Halogen free material.
Cable marking for indoor and outdoor.
Delivered with cable ties and premade holes for mounting with plastic cable ties.
Many different lengths and widths available in the assortment.

Delivery:

Delivered in package in different lengths and widths with cable ties 135x2.6 mm

Creator: Fleximark/LR	Document: DB83259091EN FLEXIMARK Character holder CAB Version: 02	Page 1 of 2
-----------------------	--	-------------

	DATA SHEET	
Valid from: 21-01-2019	FLEXIMARK® CHARACTER HOLDERS CAB	

Product data:

Part no.	Article designation	Width (mm)	Text length (mm)	Length (mm)	Content (unit)	PU	Cable ties included	Content (unit)
83259091	Character holder CAB 6-35 TR	6	35	47	50	1	135x2.6	100
83259090	Character holder CAB 6-38 TR	6	38	50	50	1	135x2.6	100
83259087	Character holder CAB 9.5-18 TR	9,5	18	30	50	1	135x2.6	100
83259088	Character holder CAB 9.5-35 TR	9,5	35	47	50	1	135x2.6	100
83259084	Character holder CAB 9.5-28 TR	9,5	28	40	50	1	135x2.6	100
83259085	Character holder CAB 9.5-38 TR	9,5	38	50	50	1	135x2.6	100
83259086	Character holder CAB 9.5-58 TR	9,5	58	70	50	1	135x2.6	100
83259083	Character holder CAB 9.5-66 TR	9,5	66	78	50	1	135x2.6	100
83259078	Character holder CAB 12-18 TR	12	18	30	50	1	135x2.6	100
83259079	Character holder CAB 12-28 TR	12	28	40	50	1	135x2.6	100
83259080	Character holder CAB 12-38 TR	12	38	50	50	1	135x2.6	100
83259081	Character holder CAB 12-58 TR	12	58	70	50	1	135x2.6	100
83259075	Character holder CAB 15-45 TR	15	45	57	50	1	135x2.6	100
83259070	Character holder CAB 19-50 TR	19	50	62	50	1	135x2.6	100

Related products

FLEXIMARK® Character holders are used together with 3M™ DYMO™ Industrial marking labels (vinyl, polyester, glue-free, nylon) and FLEXIMARK® Marking systems. All of the related products are available in FLEXIMARK® Marking assortment.

Following FLEXIMARK® Marking systems and other marking solutions are recommended for FLEXIMARK® Character holders CAB:

CAB Size (mm)	Recommended Marking systems (mm)		
6-35	3M™ DYMO™ Marking label 6		
6-38	3M™ DYMO™ Marking label 6		
9.5-18		FLEXIMARK® MINI Marking system	FLEXIMARK® Flexilabel 9,5
9.5-35	3M™ DYMO™ Marking label 9,5		
9.5-28		FLEXIMARK® MINI Marking system	FLEXIMARK® Flexilabel 9,5
9.5-38		FLEXIMARK® MINI Marking system	FLEXIMARK® Flexilabel 9,5
9.5-58		FLEXIMARK® MINI Marking system	FLEXIMARK® Flexilabel 9,5
9.5-66	3M™ DYMO™ Marking label 9,5		FLEXIMARK® Flexilabel 9,5
12-18	3M™ DYMO™ Marking label 12		
12-28	3M™ DYMO™ Marking label 12		
12-38	3M™ DYMO™ Marking label 12		FLEXIMARK® Flexilabel 12
12-58	3M™ DYMO™ Marking label 12		
15-45	3M™ DYMO™ Marking label 15		FLEXIMARK® Flexilabel 15
19-50	3M™ DYMO™ Marking label 19		FLEXIMARK® Flexilabel 19

Note:

Pictures are not to scale and do not represent detailed images of each product.

Creator: Fleximark/LR	Document: DB83259091EN FLEXIMARK Character holder CAB Version: 02	Page 2 of 2
-----------------------	--	-------------