


	<b>DATA SHEET</b>	
Valid from: 16.05.2023	<b>Marking tape DYMO®*</b>	

DYMO® marking tape is specifically designed for tough industrial environments.  
 Available in different materials and for different applications.  
 Marking tape in vinyl, polyester, nylon – also adhesive-free marking tape.  
 Very strong adhesion (does not include adhesive-free marking tape).



**Rhino version tape**

**Technical data**

Material:	Vinyl, polyester and nylon
Recommended storage:	21 °C and 50% RH, <two years
Colour:	White, Yellow, Red, Orange, Green, Blue, Violet, Brown, Grey, Black

**Mounting:**

For maximum adhesive, leave label in place for at least 24h.  
 Adhesive-free markings can be used together with FLEXIMARK® Character holders PTEF and Character holder PGS.

**Other product data:**

ETIM Classification:	EC001288
Approvals:	REACH, UL969
Colour combinations are suited to different control standards, e.g.: ANSI Z535, ISO38641, ANSI A 3.1, SO70010, ANSI606-B.	

Note: \*Trade product, no Lapp product.  
 Pictures are not to scale.

Creator: Fleximark/LR	Document: DB83259441EN Marking tape DYMO Version: 03	Page 1 of 3
-----------------------	---	-------------

	<b>DATA SHEET</b>	
Valid from: 16.05.2023	<b>Marking tape DYMO®*</b>	

ENVIRONMENT SURFACE	Heat/Cold-resistant	UV-resistant	Oil-resistant	Water-resistant	Chemical-resistant
Cable/Wire	Nylon* Shrink tube	Vinyl* Shrink tube	Vinyl* Shrink tube	Vinyl* Shrink tube	Vinyl* Shrink tube
Curved surface	Nylon* Vinyl	Vinyl* Nylon	Vinyl*	Vinyl* Nylon	Vinyl*
Flat surface	Polyester* Nylon	Polyester* Vinyl	Polyester* Vinyl	Polyester* Vinyl	Polyester* Vinyl
Structured surface	Polyester* Nylon	Vinyl* Polyester	Vinyl* Polyester	Vinyl* Polyester	Vinyl* Polyester

### Product data:

#### Vinyl, DYMO® Rhino

Flexibility, a strong adhesive and high resistance to chemicals. Suitable for many applications. The colour combinations are adapted to different Control Standards. (ANSI Z535, ISO3864, ANSI A 13.1, ISO7010, ANSI606-B). Laminated vinyl tape is provided with a laminate to wrap around the cable and over the text

E-nummer	Lapp article no.	Article designation	Width mm	Length mm	Colour	Text	PU
2972121	83259441	Vinyl 12 BK/YE	12	5.5	Yellow	Black	1
2972122	83259442	Vinyl 19 BK/YE	19	5.5	Yellow	Black	1
1693065	61800366	Vinyl 24 BK/YE	24	5.5	Yellow	Black	1
2972132	83259452	Vinyl 9 BK/WH	9	5.5	White	Black	1
2972133	83259453	Vinyl 12 BK/WH	12	5.5	White	Black	1
2972134	83259454	Vinyl 19 BK/WH	19	5.5	White	Black	1
1693052	61800361	Vinyl 24 BK/WH	24	5.5	White	Black	1
1693061	61800362	Vinyl 12 WH/RD	12	5.5	Red	White	1
1693062	61800363	Vinyl 19 WH/RD	19	5.5	Red	White	1
2972124	83259444	Vinyl 12 BK/OR	12	5.5	Orange	Black	1
2972125	83259445	Vinyl 19 BK/OR	19	5.5	Orange	Black	1
1693066	61800367	Vinyl 12 WH/GN	12	5.5	Green	White	1
1693067	61800368	Vinyl 19 WH/GN	19	5.5	Green	White	1
1693069	61800370	Vinyl 12 WH/BU	12	5.5	Blue	White	1
1693071	61800371	Vinyl 19 WH/BU	19	5.5	Blue	White	1
1693099	61800382	Vinyl 9 WH/BK	9	5.5	Black	White	1
1693101	61800383	Vinyl 12 WH/BK	12	5.5	Black	White	1
1693103	61800384	Vinyl 19 WH/BK	19	5.5	Black	White	1
<b>Laminated Vinyl</b>							
1648413	83259455	Laminated vinyl 24 BK/WH	24	5.5	White	Black	1

#### Polyester, DYMO® Rhino

Specially developed for tough industrial environment. Used on many different surfaces: smooth and textured. Strong resistance to solvents and chemicals. The colour combinations are adapted to different Control Standards (ANSI Z535, ISO3864, ANSI A 13.1, ISO7010, ANSI606-B).

E-nummer	Lapp article no.	Article designation	Width mm	Length m	Colour	Text	PU
2972135	83259460	Polyester 9 TR	9	5.5	Transparent	Black	1
1648405	83259461	Polyester 12 TR	12	5.5	Transparent	Black	1
1648406	83259462	Polyester 19 TR	19	5.5	Transparent	Black	1
2972114	83259424	Polyester 9 WH	9	5.5	White	Black	1

Creator: Fleximark/LR	Document: DB83259441EN Marking tape DYMO Version: 03	Page 2 of 3
-----------------------	---	-------------

	<b>DATA SHEET</b>	
Valid from: 16.05.2023	<b>Marking tape DYMO®*</b>	

2972115	83259425	Polyester 12 WH	12	5.5	White	Black	1
2972116	83259426	Polyester 19 WH	19	5.5	White	Black	1
1648404	83259430	Polyester 24 WH	24	5.5	White	Black	1
2972117	83259427	Polyester 9 SR	9	5.5	Silver	Black	1
2972118	83259428	Polyester 12 SR	12	5.5	Silver	Black	1
2972119	83259429	Polyester 19 SR	19	5.5	Silver	Black	1
2972495	83259465	Polyester 6mm PLP-BLK-WH-6	6	6	White	Black	1
2972497	83259467	Polyester 6mm PLP-BK-SR-6	6	6	Silver	Black	1

### Nylon, DYMO® Rhino

Specially developed for tough industrial environment. Specially designed for labeling wires and cables. The color combinations are adapted to different Control Standards (ANSI Z535, ISO3864, ANSI A 13.1, ISO7010, ANSI606-B).

E-number	Lapp article no.	Article designation	Width mm	Length mm	Colour	Text	PU
2972110	83259420	Nylon 12 WH	12	3.5	White	Black	1
2972111	83259421	Nylon 19 WH	19	3.5	White	Black	1
1648407	83259431	Nylon 24 WH	24	3.5	White	Black	1
2972112	83259422	Nylon 12 YE	12	3.5	Yellow	Black	1
2972113	83259423	Nylon 19 YE	19	3.5	Yellow	Black	1

### Note:

Pictures are not to scale and do not represent detailed images of each product.

Creator: Fleximark/LR	Document: DB8325944 1EN Marking tape DYMO Version: 03	Page 3 of 3
-----------------------	--	-------------