


83259596	DATA SHEET	
Valid from: 14.05.2024	ME550 Portable Embossing machine	

ME550 FLEXI CABLE TAG is a solution designed to mark on easy entry marker plates and tags. The unit incorporates an adjustable marker plate loader which can adapt to different marker plate sizes based on application requirements. With a completely renewed design and new features, the ME550 FLEXI CABLE TAG is an advanced solution that can be integrated into any existing factory or office network.



Technical data

Technology:	Embossing
performance:	180 tags per hour based on 12 characters
Printable area:	90 x 13,9 mm
Dimensions:	460 x 530 x 270 mm
Weight:	26 Kg
Interface:	USB 2.0 port (device and host),
Display:	7" WVGA LCD touchscreen display
Software:	FLEXIMARK® Software

Other product data:

ETIM Classification:	EC001672
Country of origin:	USA

Hardware:

System	CPU Arm Cortex-A8 / RAM 256 MB, with flash-disk and file system for Linux O.S. based
Power supply:	From 100 to 240 Volts – 50 or 60 Hz
Power consumption:	300-Watt max
Operating environment:	Temperature: 10°C to 35°C / 50°F to 95°F
Relative Humidity:	30% to 90%

Used by:


- Utility and power companies
- Shipyards
- Aircraft overhaul facilities
- Military
- Mining operations
- Industrial manufactures

Ideal for:

- | | |
|--|---|
| <ul style="list-style-type: none"> ● Pipe identification: -Water Treatment -Chemical Plants -Asset control tags -Industrial Facilities -Refineries | <ul style="list-style-type: none"> ● Cable identification: -Oil Rigs -Submarines -Mining -Cell towers -Ships & Boats -Aircrafts -Infrastructure |
|--|---|

Note: *Trade product, no Lapp product.
Pictures are not to scale.

Creator: Fleximark/JS Released: 140524	Document: DB83259596EN ME550 Embossing machine Version: 00	Page 1 of 2
---	---	-------------

83259596	DATA SHEET	
Valid from: 14.05.2024	ME550 Portable Embossing machine	

Related products:

To make a complete solution with the embossing machine we highly recommend using the material and attachments below: Acid-resistant stainless-steel markings and cable ties made of SS2348, AISI-316L steel.

The cable ties exist in sizes from 4.6x100 up to 7.9x1200 which allows a wider range of use.

After installation you can use the Stainless-steel tie plier HT-338 to automatically tighten and cut the ties to the adjusted tension force.

Article number	Description	Size	Quantity
83259597	PES cable marker blank 90x13,9	90x13,9	50/Pack
61812950	LS 4.6x200 Steel cable ties	4.6 x 200	100/Pack
61813088	LSC 4.6x200 Steel cable ties polyester coating	4.6x200	100/Pack
83250022	Stainless steel tie plier HT-338	178x140x29mm	1pcs



Note: *Trade product, no Lapp product.
Pictures are not to scale.

Creator: Fleximark/JS Released: 140524	Document: DB83259596EN ME550 Embossing machine Version: 00	Page 2 of 2
---	---	-------------