# DATA SHEET

FLEXIMARK<sup>®</sup> Thermal transfer printer EOS

### **TLEXIMARK**

Thermal transfer EOS series – one concept, two sizes. EOS2 printer is the compact for small work spaces. EOS5 prints label rolls up to 203 mm diameter. Touchscreen colour LCD display.





#### **Technical data**

Printing method: Print resolution (dpi): Display: Print width up to (mm): Print speed up to (mm/s): Material thickness (mm)/weight (g/m<sup>2</sup>): Power supply: Approval:

Temperature/humidity Operation: Temperature/humidity Stock:

#### Other product data:

ETIM Classification: Country of origin:

#### Advantages:

Combines all functions of a solid label printer with highest ease of operation.

Text with long term durability thanks to thermal transfer printing.

Thermal transfer printing method increases smudge, scratch resistance and resistance to oils and chemicals. Technical support.

User-friendly thermal transfer printer.

Many labels available in the FLEXIMARK® Marking system assortment.

### Storage:

Cool and dry in original packaging.

#### Other product data:

ETIM classification:

EC001672

	Document: DB83259599EN CAB EOS Thermal	
Creator: Fleximark/LR	transfer printer.doc	Page 1 of 5
	Version: 02	

Thermal transfer/Transfer 300 (203 on request) Touchscreen 160x255 pixel with colour 105.7 150 0,055-0.7/60-240\* 100-240 VAC, 50/60 Hz CE, FCC class A, CB, CCC, UL

+ 5 - 40°C/10 - 85% not condensing + 0 - 60°C/20 - 80% not condensing

EC001672 DE

Valid from:	
05-12-2018	

FLEXIMARK<sup>®</sup> Thermal transfer printer EOS

	Document: DB83259599EN CAB EOS Thermal	
Creator: Fleximark/LR	transfer printer.doc	Page 2 of 5
	Version: 02	

FLEXIMARK® Thermal transfer printer EOS



#### Product data:

Art no.	Description	Media core diameter (mm) ***	Media roll outside diameter up to (mm)***	Size (mm)	Weight (kg)	Packaging unit
83259599	Thermoprint EOS1/300**	38-76	152	189x322x253	4	1
83259598	Thermoprint EOS4/300**	38-76	203	245x412x264	5	1

#### Accessories CAB EOS4:

Art no	Description	Cutting height from (mm)	Cuts /min. up to	Packaging unit
83259584	Cutter thermal transfer EOS4	10	200	1



### Delivery:


Printer is delivered including USB cable, ribbon 55mm R71, FLEXIMARK<sup>®</sup> Software

	Document: DB83259599EN CAB EOS Thermal	
Creator: Fleximark/LR	transfer printer.doc	Page 3 of 5
	Version: 02	

# **DATA SHEET**

FLEXIMARK<sup>®</sup> Thermal transfer printer EOS

### *TLEXIMARK*



- 1. Touchscreen LCK display: Clearly designed for highest ease of use.
- 2. USB: 2 USB interfaces on the operation panel, 1 USB interface on the back for memory stick, service key, WLAN, Bluetooth, keyboard and scanner.
- 3. Roll holder: The label roll is inserted and centred automatically when Margin Stop is pressed on and locked.
- 4. **Ribbon retainer:** The stop is adjustable to the foil width.
- 5. **Gap or reflective sensor:** The sensor position is adjustable by the red knob via a spindle. The set position is displayed with a LED.
- 6. Label guide: The guides are adjusted to the material width with a knob.
- 7. Printhead 203 or 300dpi: The printhead can be easily removed by hand for cleaning or replacement.
- 8. Drive roller: It can be removed for cleaning or replacement without tools. As small labels may cause friction between printhead and print roller it is recommended to use in this case narrow print rollers with a width of 25, respectively 50 mm ensuring a better print image and extending the life of the printhead.





	Document: DB83259599EN CAB EOS Thermal	
Creator: Fleximark/LR	transfer printer.doc	Page 4 of 5
	Version: 02	

# DATA SHEET

FLEXIMARK<sup>®</sup> Thermal transfer printer EOS



#### **Related products:**

In the FLEXIMARK<sup>®</sup> Marking system assortment there are different wire, cable and component labels available for printing with thermal transfer printer CAB EOS1 and EOS4. Within the ribbon assortment we offer vax and vax/harts, black and white ribbon in width from 25 up to 110mm.



#### Note:

Pictures are not to scale and do not represent detailed images of each product.

Creator: Fleximark/LR transfer printer.doc Page 5 of 5   Version: 02 Page 5 of 5	Creator: Fleximark/LR	Document: DB83259599EN CAB EOS Thermal transfer printer.doc Version: 02	Page 5 of 5
--	-----------------------	---	-------------