


83284000	DATA SHEET	
Valid from: 05.10.2026	ClipMark*	

Open wire marker, available on a reel, ready to print on thermal transfer printer. A unique structure of the marker makes it really flexible and easy to mount even on bent cables. Enables fast snap installation onto already connected wires.

Print with Cab Eos thermal transfer printer, using the correct driver roll and ribbon.



Technical data:

Material:

Halogen-free, cadmium and silicone-free

Marker base: ABS

Contains Melamine (Cas no. 108-78-1) in the soft roof of the marker (6-35%).

Temperature range:

-40°C up to +90°C

Color:

Yellow, white

Certificate:

UL 94 V2 Flammability

Complies with:

EN 45545 HL2

Recommended ribbon:

R71 (83259545)

Additional features:

Available in four different sizes.

Other product data:

ETIM Classification: EC001288

*Trade product. No LAPP product.

Note: pictures are not to scale.


Creator: FLEXIMARK/LR Released: 05.10.2026/BW	Document: DB83284000EN ClipMark Version: 00	Page 1 of 3
--	--	-------------

83284000	DATA SHEET	
Valid from: 05.10.2026	ClipMark*	

Product data:

LAPP part no.	Article designation	For wire area mm ²	Diameter mm (min/max)	Length mm	Colour	Amount/role	PU
83284000	ClipMark 0.25-0.5/ 12 mm YE	0,25-0,5	1,2-1,8	12	Yellow	1400	roll
83284001	ClipMark 0.25-0.5/ 12 mm WH	0,25-0,5	1,2-1,8	12	White	1400	roll
83284002	ClipMark 0.25-0.5/ 18 mm YE	0,25-0,5	1,2-1,8	18	Yellow	900	roll
83284003	ClipMark 0.25-0.5/ 18 mm WH	0,25-0,5	1,2-1,8	18	White	900	roll
83284004	ClipMark 0.25-0.5/ 24 mm YE	0,25-0,5	1,2-1,8	24	Yellow	700	roll
83284005	ClipMark 0.25-0.5/ 24 mm WH	0,25-0,5	1,2-1,8	24	White	700	roll
83284006	ClipMark 0.75-1.5/ 12 mm YE	0,75-1,5	1,8-2,5	12	Yellow	1400	roll
83284007	ClipMark 0.75-1.5/ 12 mm WH	0,75-1,5	1,8-2,5	12	White	1400	roll
83284008	ClipMark 0.75-1.5/ 18 mm YE	0,75-1,5	1,8-2,5	18	Yellow	900	roll
83284009	ClipMark 0.75-1.5/ 18 mm WH	0,75-1,5	1,8-2,5	18	White	900	roll
83284010	ClipMark 0.75-1.5/ 24 mm YE	0,75-1,5	1,8-2,5	24	Yellow	700	roll
83284011	ClipMark 0.75-1.5/ 24 mm WH	0,75-1,5	1,8-2,5	24	White	700	roll
83284012	ClipMark 1.5-2.5/ 12 mm YE	1,5-2,5	2,5-3,3	12	Yellow	1400	roll
83284013	ClipMark 1.5-2.5/ 12 mm WH	1,5-2,5	2,5-3,3	12	White	1400	roll
83284014	ClipMark 1.5-2.5/ 18 mm YE	1,5-2,5	2,5-3,3	18	Yellow	900	roll
83284015	ClipMark 1.5-2.5/ 18 mm WH	1,5-2,5	2,5-3,3	18	White	900	roll
83284016	ClipMark 1.5-2.5/ 24 mm YE	1,5-2,5	2,5-3,3	24	Yellow	700	roll
83284017	ClipMark 1.5-2.5/ 24 mm WH	1,5-2,5	2,5-3,3	24	White	700	roll
83284018	ClipMark 2.5-4.0/ 12 mm YE	2,5-4,0	3,3-4,0	12	Yellow	1200	roll
83284019	ClipMark 2.5-4.0/ 12 mm WH	2,5-4,0	3,3-4,0	12	White	1200	roll
83284020	ClipMark 2.5-4.0/ 18 mm YE	2,5-4,0	3,3-4,0	18	Yellow	800	roll
83284021	ClipMark 2.5-4.0/ 18 mm WH	2,5-4,0	3,3-4,0	18	White	800	roll
83284022	ClipMark 2.5-4.0/ 24 mm YE	2,5-4,0	3,3-4,0	24	Yellow	600	roll
83284023	ClipMark 2.5-4.0/ 24 mm WH	2,5-4,0	3,3-4,0	24	White	600	roll

Size (mm ²)	Height (mm)	Width (mm)		
	H	W1	W2	W3
0.25-0.5	3,6	3,5	3,9	3,8
0.75-1.5	4,0	4,5	3,9	4,8
1.5-2.5	4,9	5,0	3,9	5,3
2.5-4.0	5,0	5,5	3,9	5,7



Drive Roller:

LAPP part no.	Article designation	For wire area mm ²	Diameter mm (min/max)	Amount/PU	PU
83284024	Drive roller ClipMark 0.25-0.5	0,25-0,5	1,2-1,8	1	pc
83284025	Drive roller ClipMark 0.75-1.5	0,75-1,5	1,8-2,5	1	pc
83284026	Drive roller ClipMark 1.5-2.5	1,5-2,5	2,5-3,3	1	pc
83284027	Drive roller ClipMark 2.5-4.0	2,5-4,0	3,3-4,0	1	pc



Creator: FLEXIMARK/LR Released: 05.10.2026/BW	Document: DB83284000EN ClipMark Version: 00	Page 2 of 3
--	--	-------------

83284000	DATA SHEET	
Valid from: 05.10.2026	ClipMark*	



Open wire marker for already connected wires.
Print with Cab EOS2 and EOS5 printer.
Its continuous format allows fast printing, with a max speed of 500 pcs per minute.

Related products

ClipMark can be printed using FLEXIMARK® Software and Cab EOS thermal transfer printer. Recommended ribbon R71, article number 83259545.



Creator: FLEXIMARK/LR Released: 05.10.2026/BW	Document: DB83284000EN ClipMark Version: 00	Page 3 of 3
--	--	-------------