


83252640	DATA SHEET	
Valid from: 10.10.2023	Marking Collar*	

The collar provides the label with effective scratch protection.
Elastic and flexible shape.
Can be used together with Trasp Ł Character Strips, TMB and LMB Labels.



Technical data

Material:	Available in PVC and as halogen free Polyuretan
Operating temperature:	PVC: -15°C to +70°C Halogen free: -15°C to +70°C
Colour:	Transparent
Flame retardant:	UL-94 V0

Mounting:

Thread the collars on the cables.

Other product data:

ETIM Classification: EC001288

Advantages:

Available in PVC or as Halogenfree Polyuretan.
Protects the marking from scratches.
Different sizes available.
Flexible combinations.

*Note: Trade product, no Lapp product.

Creator: Fleximark/LR	Document: DB83252670EN FLEXIMARK CollarFLEXIMARK Collar Version: 03	Page 1 of 3
-----------------------	---	-------------

83252640	DATA SHEET	
Valid from: 10.10.2023	Marking Collar*	

Product data:

Halogen free

E-nummer	LAPP Article No.	Designation	Cable Ø (mm)	Length (mm)	Colour	Quantity /PU
	83290211	Collar HF 2-4/10 mm TR	2-4	10	Transparent	1000
	83290212	Collar HF 2-4/15 mm TR	2-4	15	Transparent	1000
	83290213	Collar HF 2-4/30 mm TR	2-4	30	Transparent	500
2972257	83252693	Transparent collar HF 1.4-5/23mm	1,4-5	23	Transparent	500
	83290214	Collar HF 4-7/10 mm TR	4-7	10	Transparent	500
	83290215	Collar HF 4-7/15 mm TR	4-7	15	Transparent	500
2972261	83252694	Transparent collar HF 5-11/23mm	5-11	23	Transparent	200
2972262	83252675	Transparent collar HF 5-11/30mm	5-11	30	Transparent	200

PVC

E-nummer	LAPP Article No.	Designation	Cable Ø (mm)	Length (mm)	Colour	Quantity /PU
2972280	83252640	Cable strap collar 30mm	-	30	Transparent	200
2972243	83252641	Transparent collar 2-4/10 mm	2-4	10	Transparent	1000
2972244	83252642	Transparent collar 2-4/15mm	2-4	15	Transparent	1000
2972246	83252643	Transparent collar 2-4/30mm	2-4	30	Transparent	500
2972247	83252644	Transparent collar 4-7/10mm	4-7	10	Transparent	500
2972248	83252645	Transparent collar 4-7/15mm	4-7	15	Transparent	500
2972250	83252646	Transparent collar 4-7/30mm	4-7	30	Transparent	200
2972251	83252647	Transparent collar 6-10/10mm	6-10	10	Transparent	500
2972252	83252648	Transparent collar 6-10/15mm	6-10	15	Transparent	500
2972254	83252649	Transparent collar 6-10/30mm	6-10	30	Transparent	200
2972245	83252690	Transparent collar 2-4/23mm	2-4	23	Transparent	500
2972249	83252691	Transparent collar 4-7/23mm	4-7	23	Transparent	500
2972253	83252692	Transparent collar 6-10/23mm	6-10	23	Transparent	200
2941194	83290186	Transparent collar 3-4/15mm	3-4	15	Transparent	1000
2941195	83290187	Transparent collar 8-10/16mm	8-10	16	Transparent	500
2941196	83290188	Transparent collar 0,6-1,2/10mm	0,6-1,2	10	Transparent	1000
2941197	83290189	Transparent collar 0,6-1,2/15mm	0,6-1,2	15	Transparent	1000
	83290216	Transparent sleeve 2-4/15 mm	2-4	15	Transparent	1000
	83290217	Transparent sleeve 2-4/30 mm	2-4	30	Transparent	500

Creator: Fleximark/LR	Document: DB83252670EN FLEXIMARK CollarFLEXIMARK Collar Version: 03	Page 2 of 3
-----------------------	---	-------------

83252640	DATA SHEET	
Valid from: 10.10.2023	Marking Collar*	

Related products


FLEXIMARK® offers a various range of labels and marking materials that fits in the marking collar.



FLEXIMARK® LMB



FLEXIMARK® TMB



Trasp Ł Character Strips

Note:

Pictures are not to scale and do not represent detailed images of each product.

Creator: Fleximark/LR	Document: DB83252670EN FLEXIMARK CollarFLEXIMARK Collar Version: 03	Page 3 of 3
-----------------------	---	-------------