

	DATA SHEET	
Valid from: 2019-11-05	FLEXIMARK® Engraved signs FCC	

Engraved acrylic signs for both indoor and outdoor use, UV-resistant.
 Custom size, with or without adhesive and mounting holes.
 Many different colours and shapes.



Technical data

Material:	Laserply, acrylic laminated with foil. Lasertec, acrylic laminated with a thicker foil for extra endurance.
Thickness:	0,6 mm and 1,5 mm (standard)
Adhesive:	Acrylic based (standard), VHB: acrylic foam core and pressure sensitive adhesive.
Operating temperature:	-40°C to +80°C

Mounting:

For maximum adhesive, leave label in place for at least 24h.

Other product data:

ETIM Classification:	EC001288
----------------------	----------

Advantages:

Customized, professional signs.
 Suitable for harsh environments.
 Durable and UV-resistant.

Creator: Fleximark/LR	Document: DB83264100EN FLEXIMARK engraved signs FCC Version: 00	Page 1 of 3
-----------------------	--	-------------

	DATA SHEET	
Valid from: 2019-11-05	FLEXIMARK® Engraved signs FCC	

Product data:

Lapp article no.	Article designation	Colour sign	Text colour	Thickness (mm)	Adhesive	PU
83264100	Engraved Laserply WH/BK	White	Black	1,5	-	1 cm2
83264101	Engraved Laserply BK/WH	Black	White	1,5	-	1 cm2
83264102	Engraved Laserply YE/BK	Yellow	Black	1,5	-	1 cm2
83264103	Engraved Laserply RD/WH	Red	White	1,5	-	1 cm2
83264104	Engraved Laserply BU/WH	Blue	White	1,5	-	1 cm2
83264105	Engraved Laserply GN/WH	Green	White	1,5	-	1 cm2
83264106	Engraved Laserply BN/WH	Brown	White	1,5	-	1 cm2
83264107	Engraved Laserply OR/WH	Orange	White	1,5	-	1 cm2
83264108	Engraved Laserply OR/BK	Orange	Black	1,5	-	1 cm2
83264109	Engraved Laserply LGN/WH	Light green	White	1,5	-	1 cm2
83264110	Engraved Laserply ADH WH/BK	White	Black	1,5	Standard acrylic	1 cm2
83264111	Engraved Laserply ADH BK/WH	Black	White	1,5	Standard acrylic	1 cm2
83264112	Engraved Laserply ADH YE/BK	Yellow	Black	1,5	Standard acrylic	1 cm2
83264113	Engraved Laserply ADH RD/WH	Red	White	1,5	Standard acrylic	1 cm2
83264114	Engraved Laserply ADH BU/WH	Blue	White	1,5	Standard acrylic	1 cm2
83264115	Engraved Laserply ADH GN/WH	Green	White	1,5	Standard acrylic	1 cm2
83264116	Engraved Laserply ADH BN/WH	Brown	White	1,5	Standard acrylic	1 cm2
83264117	Engraved Laserply ADH OR/WH	Orange	White	1,5	Standard acrylic	1 cm2
83264118	Engraved Laserply ADH OR/BK	Orange	Black	1,5	Standard acrylic	1 cm2
83264119	Engraved Laserply ADH LGN/WH	Light green	White	1,5	Standard acrylic	1 cm2
83264120	Engraved Laserply VHB WH/BK	White	Black	1,5	VHB acrylic	1 cm2
83264121	Engraved Laserply VHB BK/WH	Black	White	1,5	VHB acrylic	1 cm2
83264122	Engraved Laserply VHB YE/BK	Yellow	Black	1,5	VHB acrylic	1 cm2
83264123	Engraved Laserply VHB RD/WH	Red	White	1,5	VHB acrylic	1 cm2
83264124	Engraved Laserply VHB BU/WH	Blue	White	1,5	VHB acrylic	1 cm2
83264125	Engraved Laserply VHB GN/WH	Green	White	1,5	VHB acrylic	1 cm2
83264126	Engraved Laserply VHB BN/WH	Brown	White	1,5	VHB acrylic	1 cm2
83264127	Engraved Laserply VHB OR/WH	Orange	White	1,5	VHB acrylic	1 cm2
83264128	Engraved Laserply VHB OR/BK	Orange	Black	1,5	VHB acrylic	1 cm2
83264129	Engraved Laserply VHB LGN/WH	Light green	White	1,5	VHB acrylic	1 cm2
83264130	Engraved Laserply 0,6 WH/BK	White	Black	0,6	-	1 cm2
83264131	Engraved Laserply 0,6 BK/WH	Black	White	0,6	-	1 cm2
83264132	Engraved Laserply 0,6 YE/BK	Yellow	Black	0,6	-	1 cm2
83264133	Engraved Laserply 0,6 RD/WH	Red	White	0,6	-	1 cm2
83264134	Engraved Laserply 0,6 BU/WH	Blue	White	0,6	-	1 cm2
83264135	Engraved Laserply 0,6 GN/WH	Green	White	0,6	-	1 cm2
83264136	Engraved Laserply 0,6 BN/WH	Brown	White	0,6	-	1 cm2
83264140	Engraved Laserply ADH 0,6 WH/BK	White	Black	0,6	Standard acrylic	1 cm2
83264141	Engraved Laserply ADH 0,6 BK/WH	Black	White	0,6	Standard acrylic	1 cm2
83264142	Engraved Laserply ADH 0,6 YE/BK	Yellow	Black	0,6	Standard acrylic	1 cm2
83264143	Engraved Laserply ADH 0,6 RD/WH	Red	White	0,6	Standard acrylic	1 cm2
83264144	Engraved Laserply ADH 0,6 BU/WH	Blue	White	0,6	Standard acrylic	1 cm2
83264145	Engraved Laserply ADH 0,6 GN/WH	Green	White	0,6	Standard acrylic	1 cm2
83264146	Engraved Laserply ADH 0,6 BN/WH	Brown	White	0,6	Standard acrylic	1 cm2
83264092	Engraved Lasertec WH/BK	White	Black	1,5	-	1 cm2
83264093	Engraved Lasertec BK/WH	Black	White	1,5	-	1 cm2
83264094	Engraved Lasertec BU/WH	Blue	White	1,5	-	1 cm2
83264095	Engraved Lasertec GN/WH	Green	White	1,5	-	1 cm2
83264096	Engraved Lasertec BN/WH	Brown	White	1,5	-	1 cm2

Creator: Fleximark/LR	Document: DB83264100EN FLEXIMARK engraved signs FCC Version: 00	Page 2 of 3
-----------------------	--	-------------

	DATA SHEET	
Valid from: 2019-11-05	FLEXIMARK® Engraved signs FCC	

83264097	Engraved Lasertec YE/BK	Yellow	Black	1,5	-	1 cm2
83264098	Engraved Lasertec RD/WH	Red	White	1,5	-	1 cm2
83264030	Engraved Lasertec ADH WH/BK	White	Black	1,5	Standard acrylic	1 cm2
83264031	Engraved Lasertec ADH BK/WH	Black	White	1,5	Standard acrylic	1 cm2
83264032	Engraved Lasertec ADH YE/BK	Yellow	Black	1,5	Standard acrylic	1 cm2
83264033	Engraved Lasertec ADH RD/WH	Red	White	1,5	Standard acrylic	1 cm2
83264034	Engraved Lasertec ADH BU/WH	Blue	White	1,5	Standard acrylic	1 cm2
83264035	Engraved Lasertec ADH GN/WT	Green	White	1,5	Standard acrylic	1 cm2
83264036	Engraved Lasertec ADH BN/WT	Brown	White	1,5	Standard acrylic	1 cm2
83264040	Engraved Lasertec VHB WT/BK	White	Black	1,5	VHB acrylic	1 cm2
83264041	Engraved Lasertec VHB BK/WT	Black	White	1,5	VHB acrylic	1 cm2
83264042	Engraved Lasertec VHB YE/BK	Yellow	White	1,5	VHB acrylic	1 cm2
83264043	Engraved Lasertec VHB RD/WT	Red	White	1,5	VHB acrylic	1 cm2
83264044	Engraved Lasertec VHB BU/WT	Blue	White	1,5	VHB acrylic	1 cm2
83264045	Engraved Lasertec VHB GN/WT	Green	White	1,5	VHB acrylic	1 cm2

Related Products

Ball chain, lock and S-hook.



Note:

Pictures are not to scale and do not represent detailed images of each product.

Creator: Fleximark/LR	Document: DB83264100EN FLEXIMARK engraved signs FCC Version: 00	Page 3 of 3
-----------------------	--	-------------