# DATA SHEET

Valid from: 13.12.2019

## **Brother PT-E300VP**



Industrial handheld labeling device for the professionals.

Durable robust design with rubber fittings to protect against stress.

Large backlit and graphic LCD screen.

Special features, quick dials and preset label layouts for cable marking.

384 symbols for electricity, audio / video, security and data.

Supplied with wrist strap 1 piece. 18 mm Flexible ID TZe tape, power adapter, rechargeable Li-ion battery and carrying case.

Prints labels in 3.5mm, 6mm, 12mm and 18mm widths.



#### **Technical data**

Dimensions: 134 (W) x 221 (H) x 69 (D) mm Weight: 740 g

### Other product data:

ETIM Classification: EC001288 Three years warranty.

#### **Advantages:**

The PT-E300VP has a large backlit graphic LCD display (16 characters x 3 rows), numeric keypad (QWERTY).

The smart thermal transfer printing sensor with sensor technology automatically sets the correct settings and provides accurate labels resistant to UV light, wear, temperature changes, chemicals and fluids.

The PT-E300VP also features a smart font size technology that is automatically selected to fit the correct label size.

Brothers TZe tape is available in a wide range of different variants, widths and colours.

#### Product data:

Lapp article no.	Article designation	PU
83257066	Brother PT-E300VP	1

#### Note:

Pictures are not to scale and do not represent detailed images of each product.

Creator: Fleximark/LR	Document: DB83257066 Brother PT-E300VP Version: 00	Page 1 of 1
-----------------------	---	-------------

No.: 0019/0894